

AL06-02-230 UNIVERSAL CENTRIFUGE



Centrifuges to meet your needs

- Maximum Volume 400ml (4x100ml)
- Many rotors and adapters available for both swing-out and fixed angle rotors as well as micro plate rotors (see AL06-02-400/420/430/440 and adapted buckets)
- Rotors are easy to exchange
- Runs can be limited from 10 seconds up to 99 hours 59 seconds (in steps of 10 seconds up to 59 minutes and then steps of 1 minute) or can be on permanent run.
- Encapsulated motor
- Highly versatile centrifuge to fit your every need

Centrifuge Safety features

- Rotor type recognition: manual input for adjustment before start up
- Imbalance sensor with safety shutdown mechanism
- Electronic Lid locking system prevents opening of lid while in usage
- Error mention with imbalance or other failure
- Manufactured in accordance to IEC 1010 regulations
- Corrosion resistant steel chambers
- Highly durable construction provides stability during imbalance

User friendly Operating features

- Large easy to view control panel with digital display
- Easy to adapt – first offers last used program
- Control buttons for selecting
- Speed /rcf
- Running time
- Acceleration – Deceleration
- Digital displays for pre-set or actual values
- Selectable acceleration and deceleration rates (braking can be adjusted to 10 different intensities – position 0 means no braking)